

Eaton XTD1A1A2

Catalog Number: XTD1A1A2

X Series Toggle Switch, Circuit position: ON-NONE-OFF, Single-pole, Single-throw, 20A at 125 Vac, 10A at 277 Vac, 15A at 28 Vac, 3/4 hp at 125-250 Vac, 0.250-inch spade terminal

General specifications

Product Name	Catalog Number
X Series Toggle Switch	XTD1A1A2
UPC	Product Length/Depth
786685227146	1.125 in
Product Height	Product Width
1.794 in	0.629 in
Warranty	Compliances
Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warrantied for one (1) year from the date of shipment.	RoHS Compliant
	Certifications
	UL Listed file E2702



Amperage Rating

20A at 125 Vac, 10A at 277 Vac, 15A at 28 Vac

Horsepower

3/4 hp at 125-250 V

Number Of Poles

Single-pole

Circuit position center

None

Circuit position down

Off

Circuit position up

On

Terminals

0.250 in spade

Throw type

Single-throw

Brochures

[XT Series Toggles Vehicle Controls](#)

Catalogs

[Eaton's Volume 11—Vehicle and Commercial Controls](#)

Drawings

[XT Series SP Toggle](#)

Specifications and datasheets

[Eaton Specification Sheet - XTD1A1A2](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)