



# YA32A3, 400 kcmil, AL, 1 Hole, 1/2" Stud, AL9CU

By Burndy  
Catalog # [YA32A3](#)



AL Terminal, AL9CU, Internal Chamfer, Tin Plated, Prefilled PENETROX™ A13, End Cap, UL/CSA, 90°C, Up to 35kV, Color Code, Die Index.

## Application

Wire Termination

## General

Color Code	Green
Connector Type	DUAL RATED
Die Index	472
EU RoHS Indicator	Yes
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	ALUMINUM
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	YA-A, Dual Rated
UPC	781810756003
UPC 12 Digit	7818107560033

## Dimensions

Dimension - B Length fraction	2-1/4 in
Dimension - B Length inch	2.26 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	3.11 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	156 mm
Dimension - Length Overall inch	6.15 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	2
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	0.5

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - AL Str Size	400 KCMIL
Conductor - AL Str Size Range	400 kcmil
Conductor - Copper Str Size	400 KCMIL
Conductor - Copper Str Size Range	400 kcmil
Conductor - Material	ALUMINUM / COPPER
Conductor Size	400 KCMIL
Conductor Type	CODE
Wire Size	400 KCMIL

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	2
Minimum Pack Quantity	1

## Product Assets

[3D Models - YA32A3\\_MODEL-PDF](#)  
[3D Models - YA32A3\\_MODEL-IGES](#)  
[3D Models - YA32A3\\_MODEL-STEP](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Aluminum Installation Instructions](#)  
[Sales Drawings - SD073935-01](#)

Dimension - Stud Size inch	1/2
Dimension - Thread Size	1/2
Dimension - Z inch	0.73 in
Physical Attribute - Tongue Angle	Straight



**A proud member of the Hubbell Family.**

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YA32A3-SPEC-EN | REV 6/2023