



Compression Terminal

By Burndy
Catalog # [YA4CL1BOX](#)



4 AWG CU, One Hole, #8-#10 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90° Up to 35kV, GRAY Color Code, 8 or 346 Die Index.

Application

Wire Termination

General

Color Code	Gray
Connector Type	STANDARD BARREL
Die Index	8
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none">• Chamfered• Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin Plating
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810552407
UPC 12 Digit	7818105524077

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Size fraction	#8-#10
Dimension - Bolt Size inch	0.21
Dimension - D inch	0.49 in
Dimension - Hole Size fraction	#8-#10
Dimension - Hole Size inch	0.21
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.58 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.34 in
Dimension - Pad Width inch	0.50 in
Dimension - Strip Length inch	7/8
Dimension - Stud Size fraction	#8-#10
Dimension - Stud Size inch	#8-#10

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Solid Size	#4 AWG
Conductor - Copper Str Navy Size	40 (19) Navy
Conductor - Copper Str Navy Size Range	40 (19) Navy-50 (19) Navy
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor - Material	COPPER
Conductor Size	4 AWG
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	1

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD079848](#)
[Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size inch #8,#10
Dimension - Z inch 0.24 in
Physical Attribute - Tongue Straight
Angle



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA4CLIBOX-SPEC-EN | REV 6/2023