

BURNDY Catalog Number
UPC Number

Description
Status

YAEV10
7818100278066
12-10 NYL. HVY DTY RING, #8-10
Stud
Active

Web Use
BURNDY Product Line

Dimensional

Length (in) 1.16
Tongue Type Ring
Stud Size (in) #10,#8
Pad Width (in) 0.37

Electrical

Max Voltage Rating 600

General

Product Description

Copper Terminal, Ring Tongue w/
Inspection Hole, Wire Range 12-
10 AWG, #8-#10 Stud, Nylon
Insulated, Short Barrel, Tin Plated,
600 Volts Max.

Conductor(s)

Aircraft Cable Size (Range) AN 12-AN 10
Copper Solid Size (Range) N/A
Navy Cable Size (Range) N/A
Copper Stranded (Range) 12-10

Physical

Type of Plating Tin
Connector Type Terminal
Color Code Yellow
Insulation Type Nylon
Plated (Yes or No) Y

Approvals / Certifications

Industry Standards Military Specified (Mil-
Spec),UL486
UL Listed Y
CSA Certified N
ROHS Compatible Compliant
UL Recognized N
CULUS N

Documentation

For further technical assistance, please contact us



BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175



BURNDY Catalog Number
UPC Number

YAEV10
7818100278066
12-10 NYL. HVY DTY RING, #8-10
Stud
Active

Description
Status

Web Use
BURNDY Product Line

Dimensional

Length (in) 1.16
Tongue Type Ring
Stud Size (in) #10,#8
Pad Width (in) 0.37

Electrical

Max Voltage Rating 600

General

Product Description

Copper Terminal, Ring Tongue w/
Inspection Hole, Wire Range 12-
10 AWG, #8-#10 Stud, Nylon
Insulated, Short Barrel, Tin Plated,
600 Volts Max.

Conductor(s)

Aircraft Cable Size (Range) AN 12-AN 10
Copper Solid Size (Range) N/A
Navy Cable Size (Range) N/A
Copper Stranded (Range) 12-10

Physical

Type of Plating Tin
Connector Type Terminal
Color Code Yellow
Insulation Type Nylon
Plated (Yes or No) Y

Approvals / Certifications

Industry Standards Military Specified (Mil-
Spec),UL486
UL Listed Y
CSA Certified N
ROHS Compatible Compliant
UL Recognized N
CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175