



BURNDY Catalog Number YAEV10  
 UPC Number 781810027806  
 Description 12-10 NYL. HVY DTY RING  
 Status Active

Web Use  
 BURNDY Product Line

Dimensional	
Length (in)	1.16
Tongue Type	Ring
Stud Size (in)	#10,#8
Pad Width (in)	0.37
Electrical	
Max Voltage Rating	600
General	
Product Description	Copper Terminal; Ring Tongue w/ Inspection Hole; Wire Range 12-10 AWG; #8-#10 Stud; Nylon Insulated; Short Barrel; Tin Plated; 600 Volts Max.
Conductor(s)	
Aircraft Cable Size (Range)	AN 12-AN 10
Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	12-10
Physical	
Type of Plating	Tin - Electro Plated
Connector Type	Terminal
Color Code	Yellow
Insulation Type	Nylon
Plated (Yes or No)	Y
Approvals / Certifications	
Industry Standards	Military Specified (Mil-Spec),UL486
UL Listed	Y
CSA Certified	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA  
 47, industrial Park Drive  
 Manchester NH03109

BURNDY Technical Servcies  
 47, industrial Park Drive  
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM  
 Monday - Friday  
 Phone: 000-346-4175