


# YAV12G3, Uninsulated Ring Terminal For 14 - 12 AWG, 1-Hole, 1/4" Stud

By Burndy  
Catalog # [YAV12G3](#)



Uninsulated Ring Terminal For 14 - 12 AWG.

## Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

## Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors, Industrials, Hospitals, Electric Utilities, Shipboard And Marine, Computers, Steel Mills, Mining Equipment And Other Equipment That Is Subject To Vibration Or Requiring Dependable Electrical Performance

## General

Catalog Number	YAV12G3
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810024874

UPC 14 Digit GTIN

00781810024874

## Dimensions

Dimension - B Length inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	0.97 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.16 in
Dimension - Pad Width inch	0.36 in
Dimension - Stud Size inch	1/4
Dimension - Z (inch)	0.33 in

## Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG
Conductor - Copper Solid Size Range	14 AWG-12 AWG
Conductor - Copper Str Size	14 AWG;12 AWG
Conductor - Copper Str Size Range	14 AWG - 12 AWG
Conductor Size	14 - 12 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	500
Minimum Pack Quantity	500

## Product Assets

Catalogs - BURNDY Master Catalog - Section B - Small Terminals  
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

Interactive Catalog - BURNDY Full-Line Digital Catalog  
Product Cross Section Image(s) - BUR\_YAV12G2\_LineArt  
Sales Drawings - 50094160  
Specifications - YAV12G3



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
BRDY-YAV12G3-SPEC-EN | REV 7/2025