

YC2C2

by Burndy
Catalog ID: YC2C2

Prop 65 Notice

CU Compression C Shape Compression Connector, 600 Volts to 35 Kv, 2 Sol. - 2 Str. (Run & Tap).

Features: Range-Taking Connector: Lowers Inventory Requirements, Compact Size: Easy To Tape And Insulate Connection, Manufactured From High Conductivity Wrought Copper: Provides Low Resistance And Excellent Electrical Conductivity, Economical: Provides Low Installed Cost, Conductor Size (run - Range): 2 AWG Solid - 2 AWG Stranded, Conductor Type: Run And Tap: Commercial Stranded Copper, Conductor Size (tap Range): 14 - 8 AWG Commercial Copper, Shape: C, Die Index: C Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750, Y45, Y46 Tool, U-C Die, (1), MD6 Tool, W-C Die, (2)



Product Details

General

| | |
|--------------|---|
| Application | For Range Of Copper And Making Tap Or Parallel Copper Connections |
| Die Index | C |
| Material | Copper |
| Plated | N |
| Plating Type | Unplated |
| Sub Brand | CRIMPIT |
| Trade Name | CRIMPIT™ |
| Type | YC-C Series |
| UPC | 781810111505 |
| UPC 12 Digit | 7818101115055 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Height inch | 1.05 in |
| Dimension - L Length Overall mm | 17 mm |
| Dimension - Length Overall inch | 0.67 in |

Conductor Related

| | |
|------------------------------------|----------------|
| Conductor - Copper Solid Run | 2 AWG |
| Conductor - Copper Solid Run Range | 2 AWG |
| Conductor - Copper Solid Tap | 2 AWG |
| Conductor - Copper Solid Tap Range | 2 AWG |
| Conductor - Copper Str Run | 2 AWG |
| Conductor - Copper Str Run Range | 2 Sol. - 2 Str |
| Conductor - Copper Str Tap | 2 AWG |
| Conductor - Copper Str Tap Range | 2 Sol. - 2 Str |
| Conductor Type | Cu C Sol-Size |

Certifications and Compliance

| | |
|------------------------------------|---|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | <ul style="list-style-type: none"> • UL 486A • UL486B |
| Standards - Industry Standards Met | <ul style="list-style-type: none"> • UL 486A • UL486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)