



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YGHA252N  
 7818102206100  
 CU 1/0 HVY DUTY GRD TERM  
 Active

**Web Use**  
 BURNDY Product Line

Thickness  
 B Length (in)  
 D - in  
 Pad Width (in)  
 Stud Size (Fraction)  
 E - in

**Dimensional**

0.19  
 0.83  
 3.00  
 0.91  
 1/2  
 1.75

**General**

Product Description

Copper Compression Lug, Heavy Duty, 2 Hole w/ Inspection Probe Hole, 1/0 AWG, 1/2" Stud, 1.75" Stud Hole Spacing, Short Barrel

**Conductor(s)**

Copper Solid Size (Range)  
 Copper Stranded (Range)

N/A  
 1/0 AWG

**Physical**

Type of Plating  
 Connector Type  
 Plated (Yes or No)  
 Index Number

Unplated  
 Terminal  
 N  
 14

**Approvals / Certifications**

Rated for Direct Burial  
 UL Listed  
 CSA Certified  
 ROHS Compatible  
 UL Recognized  
 CULUS  
 Industry Standards

Y  
 Y  
 Y  
 Compliant  
 N  
 N  
 UL468A-468B,UL467,IEEE 837

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175