




# YGHC34C26 Compression Grounding C-TAP Connector

By Burndy  
Catalog # YGHC34C26



Copper Compression C Connector, 300-500 kcmil, 3/4" Rod (Run) & 6 AWG(Sol) - 2/0 AWG(Str) (Tap).

## Application

For Direct Burial Cables

## General

Connector Type	Tap
Die Index	1011
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Sub Brand	HYGROUND, HYTAP
Trade Name	HYTAP™
Type	Taps
UPC	781810221068
UPC 12 Digit	7818102210688

## Dimensions

Dimension - B Length inch	0.88 in
Dimension - Height fraction	2-21/50 in
Dimension - Height inch	2.42 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

## Conductor Related

Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-3/0 AWG
Conductor - Copper Str Run	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	300 kcmil-500 kcmil
Conductor - Copper Str Tap	7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	7 AWG-2/0 AWG
Conductor - Rod Run	3/4 in
Conductor - Rod Run Range	3/4 in

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL467</li> <li>• IEEE 837</li> <li>• UL468A-468B</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	3700

## Product Assets

- [3D Models - YGHC34C26\\_MODEL-STEP](#)
- [3D Models - YGHC34C26\\_MODEL-IGES](#)
- [3D Models - YGHC34C26\\_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SD086223-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YGHC34C26-SPEC-EN | REV 8/2023