

YGHC34C34

by Burndy
Catalog ID: YGHC34C34

Prop 65 Notice

Copper Compression C Connector, 300-500 kcmil (Run & Tap).

Features: Irreversible Compression Ground Tap Figure C Connectors, Accommodates All Cable Combinations From #6 AWG Solid Through 500 KCMIL, C- Shaped Opening Permits Placing Two Continuous Parallel Cables Into Conductor Groove, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Prefilled With PENETROX Compound And Strip Sealed, Certain Sizes Are Also UL467 Listed And CSA Certified For Wire To Ground Rod, Tools, Die Set Catalog Number, And (number Of Crimps): HYPRESS: Y35, Y39, Y750, PAT750 Tool, U1011 Die, (3), Y45 Tool, S1011 Die, (3), Y46 Tool, P1011 Die, (3), Conductor Size (run - Mm): 150 - 240 SQ-MM, Die Index: 1011 Element A, Conductor Size (tap - Mm): 150 - 240 SQ-MM, Conductor Type: Run: Commercial Stranded Copper, Metric Copper, Tap: Commercial Stranded Copper, Metric Copper, Shape: C, Conductor Size (run - Range): 300 - 500 KCMIL, Conductor Size (tap Range): 300 - 500 KCMIL



Product Details

General

Application	For Direct Burial Cables
Connector Type	Tap
Die Index	1011
Material	Copper
Physical Attribute - Number of Crimps Required	3
Plated	N
Plating Type	Unplated
Sub Brand	HYGROUND, HYTAP
Trade Name	HYTAP™
Type	Taps
UPC	781810221082
UPC 12 Digit	7818102210822

Dimensions

Dimension - B Length inch	1.10 in
Dimension - Height fraction	2-81/89 in
Dimension - Height inch	2.91 in
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.10 in

Conductor Related

Conductor - Copper Str Run	300;350;400;450;500
Conductor - Copper Str Run Range	300-500
Conductor - Copper Str Tap	300;350;400;450;500
Conductor - Copper Str Tap Range	300-500

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	<ul style="list-style-type: none">• UL467• IEEE 837• UL468A-468B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)