

YGHP29C26 Figure 6 Compression Grounding Connector

By Burndy Catalog # YGHP29C26



Cu Compression Ground Rod Connector, 1/0 Str - 2/0 str, 1/2" - 5/8" Rod Dia.

Application

For Direct Burial In Earth And Concrete

General

Connector Type	Тар
51	
Die Index	997
EU RoHS Indicator	Yes
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of	1
Crimps Required	
Plated	Ν
Plating Type	Unplated
Prefilled Oxide Inhibitor	Υ
Sub Brand	HYTAP
Trade Name	HYTAP™
Туре	Taps
UPC	781810220931
UPC 12 Digit	7818102209311

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in

Conductor Related

Conductor - Copper Str Run	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Run Range	1/0 -250 kcmil
Conductor - Copper Str Tap	1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	1/0 -2/0 AWG
Conductor - Rebar Run	3 ;4
Conductor - Rebar Run Range	3 -4
Conductor - Rod Run	1/2 in;5/8 in
Conductor - Rod Run Range	1/2 in-5/8 in

Certifications and Compliance

Certification - CSA Approved Certification - ETL Certification - UL Listed Direct Burial	Yes No Yes
Certification - UL Recognized Certification - cULus Industry Standard(s) Standards - Industry Standards Met	No No Direct Burial • UL467 • IEEE 837
Standards - RoHS Compliance Status UL Listed	CM Yes
Logistics	
Carton Quantity Minimum Pack Quantity Pallet Quantity	25 1 7350

Product Assets

3D Models - YGHP29C26_MODEL-PDF 3D Models - YGHP29C26_MODEL-IGES 3D Models - YGHP29C26_MODEL-STEP Catalogs - Full Line BURNDY Catalog Customer Notices - Prop 65 Notice Sales Drawings - sd082473-01

