


Compression Splice

By Burndy
Catalog # [YS2C](#)

2 AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, BROWN Color Code, 10 Die Index



Application

Wire Splice

General

Color Code	Brown
Connector Type	LONG BARREL
Die Index	10
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS, Long Barrel
UPC	781810507001
UPC 12 Digit	7818105070011

Dimensions

Dimension - B Length inch	1.22 in
Dimension - L Length Overall mm	72 mm
Dimension - Length Overall inch	2.82 in
Dimension - Strip Length inch	1-5/16

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	60 (37) Navy
Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG
Conductor Type	CODE
Wire Size	#2 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1

Product Assets

[3D Models - YS2C_MODEL-IGES](#)
[3D Models - YS2C_MODEL-PDF](#)
[3D Models - YS2C_MODEL-STEP](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD007774-01](#)