

## Compression Splice

By Burndy  
Catalog # [YS30L](#)

300 kcmil CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, WHITE Color Code, 17 or 298 Die Index.



### Application

Wire Splice

### General

Color Code	White
Connector Type	STANDARD BARREL
Die Index	17
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS-L, Standard Barrel
UPC	781810508152
UPC 12 Digit	7818105081522

### Dimensions

Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.06 in
Dimension - L Length Overall mm	63 mm
Dimension - Length Overall inch	2.47 in
Dimension - Strip Length inch	1-1/8

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper Str Compact Size	300
Conductor - Copper Str Size	300 kcmil
Conductor - Copper Str Size Range	300 kcmil
Conductor - Material	COPPER
Conductor Size	300 KCMIL
Conductor Type	CODE
Wire Size	300 kcmil

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	6
Minimum Pack Quantity	1

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD022390-01](#)