

## YS30L

by Burndy  
Catalog ID: YS30L

Prop 65 Notice

Cu Comp Butt Splice(Code), 300 Navy, 300 kcmi(Com'l Cable), 600 V-35 kV, 2.47" L, Std bbl, Tin Plated, White.

Features: Standard Barrel Length, Ideal For Limited Space Applications While Providing Ample Barrel Length For Proper Crimp, Four (4) Center Conductor Stops, Provides A Center Wire Stop For Proper Conductor Insertion, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD7-34R Tool, W30CVT Die, (2), Y35, Y39, Y750, Y46 Tool, U30CRT Die, (2), Die Index: 17 Element A, Color Code: White, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (2), Wire Strip Length: 1-1/8 IN



## Product Details

### General

Application	For Limited Space Applications
Color Code	White
Connector Type	Splice
Die Index	17;298
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS-L, Standard Barrel
UPC	781810508152
UPC 12 Digit	7818105081522

### Dimensions

Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.06 in
Dimension - L Length Overall mm	63 mm
Dimension - Length Overall inch	2.47 in
Dimension - Strip Length inch	1-1/8

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Compact Size	300
-------------------------------------	-----

Conductor - Copper Str Size	300 kcmil
-----------------------------	-----------

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)