


Compression Splice

By Burndy
Catalog # [YS36](#)

600 kcmil CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, GREEN Color Code, 22 or 472 Die Index.



Application

Wire Splice

General

Color Code	Green
Connector Type	LONG BARREL
Die Index	22
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS, Long Barrel
UPC	781810526255
UPC 12 Digit	7818105262555

Dimensions

Dimension - B Length inch	2.63 in
Dimension - L Length Overall mm	149 mm
Dimension - Length Overall inch	5.85 in
Dimension - Strip Length inch	2-11/16

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	600 kcmil
Conductor - Copper Str Size Range	600 kcmil
Conductor - Material	COPPER
Conductor Size	600 KCMIL
Conductor Type	CODE
Wire Size	600 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6
Minimum Pack Quantity	1

Product Assets

[3D Models - YS36_MODEL-IGES](#)
[3D Models - YS36_MODEL-STEP](#)
[3D Models - YS36_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD007774-01](#)