

ZTL SERIES



- · LED Rated
- MOV surge protection, 105 – 305V
- 8 amp electronic ballast for LED
- · 15-year warranty

WOS SERIES



- · LED Rated
- Automatic ON/OFF, energy saving walk-through, or test
- 6 different settings:5, 10, 25, 20, 25 and 30 minutes

SS703Z SERIES



- · LED Rated
- 7-day Sunset/Sunrise programming
- No neutral required
- 3-way switch compatible

1109A SERIES



- · LED Rated
- Mechanical time switch SPST and DPST combination
- Multi-Voltage 120/208-277V

LED RATED PRODUCTS

PHOTOS	PRODUCT	DESCRIPTION	PHOTOS	PRODUCT	DESCRIPTION (LED RATED)
	1109A-(O) Series	Mechanical Time Switch 24Hr, 120/208-277VAC (O) - Outdoor Enclosure 40A General/16A LED/5HP	000	COS-L Series	PIR Ceiling Mount 24VDC TRP Power Pack Required 5-30 Min Delay/1200sq. Ft.
	E100 Series	1CH Digital Time Switch 24Hr, 120-277VAC 40A General/16A LED/5HP	(a)	COS-L2T Series	Ultrasonic/PIR Ceiling Mount 24VDC TRP Power Pack Required 5-30 Min Delay/1200sq. Ft.
The state of the s	EWZ201C Series	1 or 2CH Digital Time Switch 7-Day Astronomic, 120-277VAC 30A General/16A LED/2HP		TRP-24I Series	TRP Power Pack for Sensors 120-277VAC to 24VDC Neutral Required 15A General/LED/1HP
	5401A Series	3PST Contactor, 120VAC Coil 40A General/40A LED/7.5HP		3000 Series	Flush Mount Photocontrol 120 or 208-277VAC Fail on/Delay on/off 15A General/600VA LED
e	SS720Z Series	Digital In-Wall 7-Day Astronomic, 120VAC 15A General/LED		2129A Series	1/2" Conduit Mount Photocontrol 120/208-277VAC, 190J MOV Fail on /Die Cast Zinc 15A General/1400VA LED
	SS703Z Series	Digital In-Wall/No Neutral 7-Day Astronomic, 120-277VAC 15A General/8A LED/3-Way		2119A Series	1/2" Conduit Mount Photocontrol 120/208-277VAC Fail on/Die Cast Aluminum 15A General/1400VA LED
	R5M4HW Series	Auto Off Countdown Timer 120VAC In-Wall, 5/10/30 Min - 1/2/4 Hr 15A General/LED/1/2HP		2000 Series	1/2" Fixed Position Photocontrol 120 or 208-277VAC Fail on/Lexan® Housing 15A General/1400VA LED
9	SS403 Series	Auto Off Countdown Timer 120-277VAC Digital In-Wall/No Neutral 15A/1200W, LED/3-Way		2001 Series	1/2" 180° Swivel Photocontrol 120 or 208-277VAC Fail on/Lexan® Housing 15A General/1400VA LED
	WOS-M(N) Series	PIR Wall Switch 120-277VAC/Zero Cross (N) Neutral Required 15A General/8A LED/1/4HP	1000	2020 Series	1/2" 180° Swivel Photocontrol 120 or 208-277VAC Fail on/Lexan® Housing 15A General/1400VA LED
3.30	WOS-M(N)2R Series	PIR Wall Switch Two Relay 120-277VAC/Zero Cross (N) Neutral Required 15A General/8A LED/1/4HP		5237-UL Series	Turn-Lock Photocontrol 105-305VAC, 510J MOV, Fail on 15A General/4A LED/1800VA Bal
	WOS-MN2T Series	Ultrasonic/PIR Wall Switch 120-277VAC/Zero Cross Neutral Required 15A General/8A LED/1/4HP		ZTL124(F) Zero Cross Long Life Series	Turn-Lock Photocontrol 105-305VAC, 510J MOV Fail on or (F) Fail off 15A General/8A LED/1800VA Bal
	COS-M Series	PIR Ceiling Mount 120-277VAC/Zero Cross Neutral Required 15A General/8A LED/1/4HP		5400A Series	Contactor with TL Photocontrol 120, 208-240, 277VAC Fail on/3PST 40A General/40A LED

