

Eaton R9000 FF

Catalog Number: R9000 FF

Eaton B-Line series bussed gutter and termination cabinets, 1200 A, 3R, Underground, ANSI 61 gray painted, 065 kAIC, 6 Studs / Ø, (4) #4 - 600 MCM, Galvanized steel, Surface mount, 4 wires, 3 phase



Photo is representative

General specifications

| | |
|--|----------------|
| Product Name | Catalog Number |
| Eaton B-Line series bussed gutter and termination cabinets | R9000 FF |
| | UPC |
| | 782051531947 |
| Product Length/Depth | Product Height |
| 11 in | 52 in |
| Product Width | Product Weight |
| 36 in | 230 lb |
| Compliances | Certifications |
| EUSERC Approved | UL |

Electrical specifications

Amperage Rating

1200 A

Phase

Three-phase

Interrupt rating

65 kAIC

Material/finish

Material

Galvanized steel

Finish

ANSI 61 gray paint

Model

Number of wires

4

Feed type

Underground

Mounting method

Surface

Line lug size

6 studs/Ø

Load lug size

(4) #4 - 600 MCM

Special features

Used as a termination point before bussed gutters

Standards

Degree of protection

3R

Resources

Catalogs

[universal bussed gutters](#)

[bussed gutters](#)

Specifications and datasheets

[Eaton Specification Sheet - R9000 FF](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)