

# Eaton CHU1NSFEMA

Catalog Number: CHU1NSFEMA

Eaton pedestal mount unmetered, Unmetered, 50A, None, None, Non-ground fault, None, None, CH, Top, Surface, Circuits: 4, NEMA 14-50R, None, None, 4, 0, 0, 125/250V, None, None

## General specifications



**Product Name**

Eaton pedestal mount unmetered

**Catalog Number**

CHU1NSFEMA

**UPC**

782116910205

**Product Length/Depth**

4.3 in

**Product Height**

17.1 in

**Product Width**

9.5 in

**Product Weight**

8.25 lb

**Warranty**

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Certifications**

UL Listed file E163588  
UL 231

**Catalog Notes**

Replaces CHU1NS.

Type

Unmetered

Receptacle center

None

Receptacle left

NEMA 14-50R

Receptacle right

None

Circuit breaker type

CH

Feed type

Top

Mounting

Surface

Number of circuits

4

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHU1NSFEMA](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
  
All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)