

Eaton DH221NGK

Catalog Number: DH221NGK

Eaton Heavy duty single-throw fused safety switch, Enhanced visible blade, 30 A, NEMA 1, Painted steel, Class H, neutral, Two-pole, Three-wire, 240 V, Max Hp: 1.5, 3 hp/3, 7.5 hp/5 hp (1,3PH @ Std fuse/time delay/250 Vdc), #14-#2 Cu/Al

Photo is representative

General specifications

Product Name	Catalog Number
Eaton heavy duty fusible safety switch	DH221NGK
UPC	Product Length/Depth
782113205342	16.5 in
Product Height	Product Width
8.5 in	9.5 in
Product Weight	Warranty
16 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL Listed	3-Phase hp ratings shown are grounded B phase ratings; UL listed



Physical Attributes

Enclosure

NEMA 1

Enclosure material

Painted steel

Fuse class provision

Class H

Fuse configuration

Fusible with neutral

Number Of Poles

Two-pole

Number of wires

3

Type

Heavy duty fusible safety switch

Performance Ratings

Amperage Rating

30A

HP rating - max

1.5, 3 hp/3, 7.5 hp/5 hp (1,3PH @ Std fuse/time delay/250 Vdc)

NEMA rating

NEMA 1

Voltage rating

240V

Miscellaneous

Product Category

Heavy Duty, Fusible with neutral

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH221NGK



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia