



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UGP20231 20 Amp 2W 3P 125V Plug 3/4 Hub SGL Gang Dead End

Hubbell--Killark

Catalog Number	UGP20231
Manufacturer	Hubbell--Killark
Description	Ugp Series - Aluminum 20 Amp 125VAC Interchangeable Blade Style Plug -Nema Configuration 5-20P
Weight per unit	0.5000 (lbs/each)
Product Category	Wiring Devices

Features

amperage rating	20
Cord Type	S, SO, ST, or STO
Material	Copper-Free Aluminum
Number of Wires	3
Phase	1
Poles	2
Voltage Rating	125
Wire Size	#12 or #14 AWG

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	1.69" H x 1.69" W x 3.36" L
------	-----------------------------

Descriptions

Description	20 AMP 2W 3P 125V PLUG 3/4 HUB SGL GANG DEAD END
extra long description	KLRK UGP-20231 20A PLUG 5-20P
Long Description	UGP SERIES - ALUMINUM 20 AMP 125VAC INTERCHANGEABLE BLADE STYLE PLUG -NEMA CONFIGURATION 5-20P
Product Type	20A Plug 5-20P
Special Features	ACCEPTOR plugs conform to NEMA configurations and can be used with standard receptacles in non-hazardous areas to maximize equipment utilization. The system's "turn to engage" feature locks in plug and can be used to prevent accidental disengagement of cr

Manufacturer Information

Brand	KILLARK
GTIN	00783936991955
Manufacturers Part Number	UGP-20231
sub brand	ACCEPTOR
UPC	783936991955



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Aluminum interchangeable blade style plug

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	0.5

Uses, Certifications, and Standards

Application	Petroleum refineries, chemical plants, wet/damp areas, corrosive environments, petroleum plants, grain elevators/feed mills, flour and feed mills, and indoor or outdoor locations
environmental conditions	Wet and hazardous locations
nema rating	5-20P; NEMA 3, 7BCD, 9FG
standard	UL, CSA