

# **FEATURES & SPECIFICATIONS**

# INTENDED USE

For use with housings LCP, LC6, L7X, L7XR, L7XF, L7XFR and L7XPR.

## CONSTRUCTION

Aluminum one-piece reflector.

White polyester powder coat paint.

Brushed nickel and white finishes are one-piece aluminum reflectors with integral flange.

Baffles available in black and white.

# INSTALLATION

Socket to trim interface.

Retaining clips riveted to top of reflector hold trim inside housing.

## LISTINGS

UL Listed to US and Canadian safety standards.


Damp location listed.

## WARRANTY

1-year limited warranty. Complete warranty terms located at <a href="https://www.acuitybrands.com/CustomerResources/Terms">www.acuitybrands.com/CustomerResources/Terms</a> and conditions.aspx

Actual performance may differ as a result of end-user environment and application.

Note: Specifications subject to change without notice.




6" Finishing Trim



BAFFLE SHALLOW

Wide Flange



Specifications

Height: 5-3/8 (13.7)

Lamp opening: 4-5/8 (11.7)

Diameter: 7-3/4 (19.7)

All dimensions are inches (centimeters) unless otherwise indicated.



ORDERING INFORMATION

For shortest lead times, configure product using **bolded options**.

Example: CB1

CB1					
Series	Finish	inish			
CB1	(blank)	White reflector with black baffle			
	W	White reflector with white baffle			
	BN	Brushed nickel reflector with black baffle			

Housing Compatibility: Housing and trim ordered separately.						
Application	Source	Maximum wattage	Housing			
		75 PAR30				
16	Incandescent	65 BR30	LCP, LC6, L7X, L7XR, L7XPR			
IC		40 A19				
	Fluorescent	13DTT	L7XF, L7XFR			

DOWNLIGHTING CB1

