



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WP3476BE Cat 6 QC A/B Keystone Con BL (M10)

Pass & Seymour/Legrand

Catalog Number	WP3476BE
Manufacturer	Pass & Seymour/Legrand
Description	Keystone Insert, Snap-In Connection, 6 Category Level, Blue, 1.18 In Length, 0.665 In Width, 0.87 In Height, -10 °C Operating Temperature, +60 °C Operating Temperature, 0.04 LB
Weight per unit	0.0402 (lbs/each)
Product Category	Outlets, Jacks, & Plates

Features

connection	RJ45 Female
insulation	Electrical Insulation Resistance: 500 (@ 100 VDC)

Material, Color, and Finish

Finish	Smooth plastic
--------	----------------

Dimensions and Weight

Size	0.76 x 0.67 x 1.18 (19.30 x 16.9 x 30)
------	--

Descriptions

Description	CAT 6 QC A/B KEYSTONE CON BL (M10)
extra long description	OnQ WP3476BE CAT 6 QC A/B KEYSTONE

Manufacturer Information

GTIN	00804428036722
Manufacturers Part Number	WP3476BE
sub brand	Legrand-On-Q
UPC	804428036722

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	RJ45 Female Cat 6 Keystone Insert

Packaging

Carton	10
Package	60
Weight Per each	0.0402

Uses, Certifications, and Standards

Application	Residential
Enclosure	Housing Material: High Impact Flame Retardant Plastic
environmental conditions	0 to 93 (relative humidity, non-condensing)
Mounting	Keystone opening
standard	ANSI/TIA-568-C.2
Temperature Rating	14 to 140 F (-10 to 60 C)