

Stylus® Alkaline Battery-Powered Pen Light

Case Material: Water-proof, machined aluminum case with anodized finish and non-slip, knurled grip comes in black, gold or silver, red, blue, US Flag

Dimensions: Length: 6.21"; 15.17 cm Diameter: 0.375"; 0.95 cm

Weight: 1.1 oz; 31.19 grams*

Light Source: High-intensity Solid-State 100,000 hour Light Emitting Diode (LED)
LED available in Arctic White, Flame Red, Ice Blue, Navigation Green,
or Ultra Violet

Light Output: 10 lumens (White LED); 1.13 lumens (Red LED); .71 lumens (Blue LED);
2.6 lumens (Green LED); 365nm (UV)

On/Off: Features a momentary blink switch and constant "on"

Run Time: Up to 60 hours

Battery: 3 "AAAA" size alkaline batteries.

Features:

- Waterproof
- Individually serialized
- Pocket clip
- Glare Guard Protector (Included)

Approvals**: UL Classified: Intrinsic Safety for Hazardous Locations; Class I, Div.1, Groups A,B,C,D, T3C
"Classified" (applies only to Black case/White LED combination)

C-UL UL Classified: Intrinsic Safety for Hazardous Locations; Class I, Div.1, Groups A,B,C,D, T3C;
"Exia" (applies only to Black case/White LED combination)

ATEX: II 1G EEx ia IIC T1; DEMKO 04 ATEX 0410949 (applies only to Black case/White or
Blue LED combinations)

Most models meet applicable European Community Directives.

Warranty: Limited lifetime warranty.

*With battery (included in purchase).

**See product for specific ratings.



Item		UPC	Part #
<i>English packaging</i>			
Stylus	Black with Red LED	080926-65006-0	65006
Stylus	Black with Blue LED	080926-65022-0	65022
Stylus	Black with Green LED	080926-65020-6	65020
Stylus	Black with White LED	080926-65018-3	65018
Stylus	UL Listed Black with White LED	080926-65058-9	65058
<i>See reverse for additional part numbers</i>			