

LED A19 ECO STYLE



Long Lasting and Energy Saving

Topaz LED Eco Style A19 lamps are ideal for both residential and commercial settings including down lights, wall sconces, ceiling fans, table and floor lamps. Dimmable down to 10% for additional energy savings and ambiance control.

FEATURES

- 230° beam spread
- 85% energy savings compared to 60W incandescent
- Long life - up to 10X longer than traditional incandescents
- RoHS compliant and mercury free
- Plastic lens material provides shatter protection

SUGGESTED APPLICATIONS

- Fan lights, decorative, recessed, task lighting
- Residential, hospitality, retail, restaurants, commercial





Job Name/Title: _____ Catalog Number _____
Contractor: _____ Notes: _____

LED A19 ECO STYLE

GENERAL SPECIFICATIONS

Input Voltage: 120V
Average Rated Life: 15,000 Hours
Base: Medium E26
CRI: 80
THD: <15%
Beam Angle: 230°
Equivalent Wattage: 60W A19
Ambient Operating Temp: -4°F to 104°F



ITEM SPECIFICATIONS / ORDER INFO

Catalog Number	Order Code	UPC	Shape	Wattage	CCT	Initial Lumens	Dimmable	PK-QTY
LA19/9/827/ECO/D	79686	751338005341	A19	9W	2700K	800	Y	8/80
LA19/9/830/ECO/D	79687	751338005358	A19	9W	3000K	800	Y	8/80
LA19/9/840/ECO/D	79688	751338005365	A19	9W	4000K	800	Y	8/80
LA19/9/850/ECO/D	79689	751338005372	A19	9W	5000K	800	Y	8/80

Not for sale in California.

NOMENCLATURE

Example: **LA19/9/827/ECO/D**

LA19 = LED A19 Shape / **9** = 9 Watt / **827** = 2700K / **ECO** = Economy / **D** = Dimmable
/ **830** = 3000K
/ **840** = 4000K
/ **850** = 5000K

ENERGY SAVINGS

	LED Wattage	Incandescent Wattage	Energy Saving, Watts	Yearly Saving, Fixture	5 Year Cost Savings
Based on 3 hours/day and \$0.11/kWh					
LA19/9/XXX/ECO/D	9W	60W	51W	\$10.24	\$51.20

NOTES:

This device is not intended for use with emergency exits. Not for use in totally enclosed fixtures.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Specifications subject to change without notice.

FIVE (5) YEAR LIMITED WARRANTY: TOPAZ LIGHTING CORP. warrants to the original purchaser that all TOPAZ LED lamps shall be free from defects of material and workmanship for a period of five (5) years from the date of purchase. Based on 12 hours of use per day. TOPAZ LIGHTING CORP. will, at its option, repair or replace without charge a defective LED lamp that has not been misused, carelessly handled or improperly installed. Repair or replacement, as stated above, shall constitute the purchaser's exclusive warranty, which does not extend to transportation, installation, labor or any other consequential charges. www.topaz-usa.com

Specifications subject to change without notice.

Revised July 2020