GE Lighting

45144 - GE crystal clear 25 watt T10 1-pack

25T10 CD1-5PK

- Add a decorative touch by using GE Crystal Clear bulbs in chandeliers, sconces or anywhere the bulb is visible.
- GE's Crystal Clear Tubular Lights are ideal for appliances, aquariums, cabinet lights and picture lights.
- 2500K soft white light appearance
- Estimated yearly energy costs $3.01 based on 3 hours per day $0.11 per kWh
- Lasts 0.9 years based on 3 hours per day usage
- T10 shape with medium base for use in picture frames, desk lamps and kitchen appliances
- Add sparkle to your fixtures with GE crystal clear bulbs. GE crystal clear tubular bulbs are perfect for highlighting artwork in picture frames, desk lamps and kitchen appliances

GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Bulb Finishes and Colors	Clear
Filament	C-8
Rated Life Hours-nominal	1000 h
Primary Application	Display Lights <Residential>
Product Technology	Incandescent
Base	E26
Bulb Shape	T10

PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	250 lm

PRODUCT INFORMATION

Product Code	45144
Description	25T10 CD1-5PK
Alternative Unit Of Measure	CASE

DIMENSIONS

Diameter	0.62 in

ELECTRICAL CHARACTERISTICS

Wattage	25 W
Input Voltage [nom]	130 V

GE Lighting

45144 - GE crystal clear 25 watt T10 1-pack

25T10 CD1-5PK

- Add a decorative touch by using GE Crystal Clear bulbs in chandeliers, sconces or anywhere the bulb is visible.
- GE's Crystal Clear Tubular Lights are ideal for appliances, aquariums, cabinet lights and picture lights.
- 2500K soft white light appearance
- Estimated yearly energy costs $3.01 based on 3 hours per day $0.11 per kWh
- Lasts 0.9 years based on 3 hours per day usage
- T10 shape with medium base for use in picture frames, desk lamps and kitchen appliances
- Add sparkle to your fixtures with GE crystal clear bulbs. GE crystal clear tubular bulbs are perfect for highlighting artwork in picture frames, desk lamps and kitchen appliances

GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Bulb Finishes and Colors	Clear
Filament	C-8
Rated Life Hours-nominal	1000 h
Primary Application	Display Lights <Residential>
Product Technology	Incandescent
Base	E26
Bulb Shape	T10

PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	250 lm

PRODUCT INFORMATION

Product Code	45144
Description	25T10 CD1-5PK
Alternative Unit Of Measure	CASE

DIMENSIONS

Diameter	0.62 in

ELECTRICAL CHARACTERISTICS

Wattage	25 W
Input Voltage [nom]	130 V