



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 744 70 CFM Recessed Fan Light

Broan/Nutone LLC

Catalog Number	744
Manufacturer	Broan/Nutone LLC
Description	Recessed Ventilation Duct Fan and Light, 4 In Duct Size, 70 CFM Air Flow, 120 V, 1.2 A, 70 CFM, Incandescent Light, 75 W, 1.5 Sones Sound Level, 12-3/4 In Length, 8-1/4 In Width, 6-7/8 In Height, Rugged 26 Gauge Galvanized Steel Housing Material, Matte White, 65 SQ.FT Ventilation Area, 9.4 LB
Weight per unit	9.4 (lbs/each)
Product Category	Combination Fans, Lights & Hea

### Features

fan type	Ventilation
housing dimensions	8-1/4 IN Length X 12-3/4 IN Width X 6-7/8 IN Height

### Descriptions

Description	70 CFM RECESSED FAN LIGHT
Special Features	Recessed fan lights disappear into the ceiling with other recessed lights, so they are practical decorating and air removal solutions for any room in the house; Not for use over cooking surfaces; Polymeric construction with matte white finish 7.375 IN trim ring baffle, its recessed styling, mounts flush with finished ceiling; Plug-in, permanently lubricated, motor with low RPM for quiet operation; Dynamically balanced centrifugal blower wheel for quiet, efficient performance; Rugged 26 GA galvanized steel

### Manufacturer Information

Brand	BROAN
GTIN	00026715163014
sub brand	LoProfile
UPC	026715163014

### Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	Recessed Fan With Light

### Packaging

Carton	1
Weight Per each	9.4

### Uses, Certifications, and Standards

standard	UL Listed For Use Over Bathtubs And Showers When Connected To A GFCI Protected Branch Circuit With PAR30L Or PAR30LN Bulbs, C/US UL Listed, HVI 2100 Certified
----------	--