



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F28T8XLSPX41ECO 28W T8 48" 4100K 86 Cri Bi-Pin Energy Saving

*Ge By Current Lamps*

Catalog Number	F28T8XLSPX41ECO
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, G13 Medium Bi-Pin Base, T8 Bulb Shape, 82, 45000 H Average Life, 4100 K, 28 W, 2725 LM Brightness (Lumens), Soda Lime Housing Material, 1.0 In Diameter, 48.0 In Length, Instant;Rapid, 0.56 LB
Weight per unit	0.5600 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

Base	Medium Bi-Pin (G13)
lumens	2675.0
Wattage	28.0

### Material, Color, and Finish

color rendering index (cri)	82.0
-----------------------------	------

### Dimensions and Weight

Length	48.0
--------	------

### Descriptions

Description	28W T8 48" 4100K 86 CRI BI-PIN ENERGY SAVING
extra long description	GEL F28T8/XLSPX41ECO 72866 FLUORESC

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168728669
UPC	043168728669

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

### Packaging

Carton	1
Package	36
Weight Per each	0.56

### Uses, Certifications, and Standards

Application	Energy Saving
-------------	---------------