ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

VM3537 .5HP 3420RPM 3PH 60HZ , 56C 3410M Tefc F1 Motor

Baldor/Abb Motors & Mechanical

Catalog Number	VM3537
Manufacturer	Baldor/Abb Motors & Mechanical
Description	Baldor Electric; Ac Motor; Phase: 3 PH; Voltage Rating: 230/460 Vac; Torque Rating: 0.75 LB-FT Full Load, 3.4 LB-FT Break Down, 2.7 LB-FT Pull-Up, 3 LB-FT Locked-Roter At 460 V, 60 HZ, 0.5 HP; Horsepower: 0.5 HP; Speed Rating: 3450 RPM; Frequency Rating:
Weight per unit	20.0 (lbs/each)
Product Category	Motors

Features

Base	No mounting
frame	56 V
horsepower	0.5 in
Insulation Class	F
Phase	3 in
Power Factor	0.63 in
Service Factor	1.25 IN
Speed Rating	3,450 rpm
Voltage Rating	230/460 V

Descriptions

Description	.5HP 3420RPM 3PH 60HZ ,56C 3410M TEFC F1 MOTOR
extra long description	BALDOR VM3537 .5HP,3450RPM,3PH,60HZ
Long Description	Baldor Electric; AC Motor; Phase: 3 PH; Voltage Rating: 230/460 VAC; Torque Rating: 0.75 LB-FT Full Load, 3.4 LB-FT Break Down, 2.7 LB-FT Pull-Up, 3 LB-FT Locked-Roter At 460 V, 60 HZ, 0.5 HP; Horsepower: 0.5 HP; Speed Rating: 3450 RPM; Frequency Rating:
Product Type	.5HP, 3450RPM, 3PH, 60HZ, 56C, 3410M, Tefc, F1
Special Features	.5HP,3450RPM,3PH,60HZ,56C,3410M,TEFC,F1

Manufacturer Information

Brand	Baldor/Abb Motors & Mechanical
GTIN	00781568109540
Manufacturers Part Number	VM3537
UPC	781568109540

Taxonomies, Classifications, and Categories

Category Description	Motors
Type	AC Motors

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	20

Uses, Certifications, and Standards

Application	General Purpose
Enclosure	TEFC
Frequency Rating	60 Hz
Mounting	F1