Product specifications

Eaton CHQ120

Catalog Number: CHQ120

3/4" Thermal magnetic circuit breakers,Type CHQ 3/4-Inch classified replacement breaker,Ground fault,20 A,10 kAIC,Single-pole,120/240V,CHQ,(1) #14-8 AWG, (2) #14-10 AWG Cu/Al,CHQ,Type CH Loadcenters



General specifications

Product Name
Eaton Classified 3/4" thermal magnetic circuit breaker

Catalog Number
CHQ120

UPC
782113010823

Product Length/Depth
2.5 in

Product Height
2.7 in

Product Width
0.7 in

Product Weight
0.3 lb

Warranty
Limited lifetime residential, 1 year commercial

Certifications
UL 489

Catalog Notes
Replacement for Square D Type QO Breakers. Requires one 3/4-inch (19.1 mm) space.

Powering Business Worldwide

defaultTaxonomyAttributeLabel

Type

Type CHQ 3/4-Inch classified replacement breaker

Special features

Ground fault

Amperage Rating

20 A

Voltage rating

120/240 V

Circuit breaker type

CH

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CHQ

Wire size

(1) #14-8 AWG

(2) #14-10 AWG Cu/Al

Number of poles

Single-pole

Resources

Brochures

Loadcenters and Circuit Breakers

Standard circuit breaker catalog numbers - 5651B63SH09

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - CHQ120

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia