shat-r-shield® INC.
The Protective Lighting Company

01591S

80PAR38/HAL/IR/NFL25DL120VSIL(PKX



Average Life Hours: 3000

Base: Medium (E26)

Beam Angle: 25 DEG

Bulb: PAR38

Coating: Silicone

Color Temperature: 2900 K

CRI: 100

Diameter: 4.75 IN

Initial Lumens: 1545 LM

Lamp Type: Halogen

Length: 5.31 IN

Mean Design Lumens: 1545 LM

Pack By: 10

Shape: PAR38

Special Features: Shatter-Resistant

Type: Halogen

UPC: 726585015917

Voltage: 120.0 V

Wattage: 80.0 W