



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



127TB 200A 7T RT Ou Meter Socket

Milbank

Catalog Number	127TB
Manufacturer	Milbank
Description	7 Term RNGTP 2 SML CLS PLT LNK Byps 200 Amp
Weight per unit	36.0 (lbs/each)
Product Category	Test Block Bypass Meter Socket

Features

amperage rating	200 Continuous Ampere
Bypass Type	Link Bypass
Cable Entry	Overhead or Underground
cutout size	No Main Breaker
insulation	Fiberglass with Resin
Phase	3 Phase
Voltage Rating	Up to 600 Volts Alternating Current

Dimensions and Weight

Size	6L x 14.125W x 30H
------	--------------------

Descriptions

Also Known As...	Meter Socket
	Meter Box
Description	200A 7T RT OU METER SOCKET
extra long description	MILB 127TB 200A 7T RT OU 10249
Long Description	7 TERM RNGTP 2 SML CLS PLT LNK BYPS 200 AMP
Product Type	200A 7T RT Ou 10249

Manufacturer Information

Brand	MILBANK
GTIN	00784572102491
Manufacturers Part Number	127TB
UPC	784572102491

Taxonomies, Classifications, and Categories

Category Description	Meter Sockets
Type	Ring Type Meter Socket

Packaging

Carton	1
Weight Per each	36



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Meter Socket
Enclosure	G90 Galvanized Steel with Powder Coat Finish
Frequency Rating	60 Hertz
Mounting	Surface Mount
standard	UL Listed; Type 3R