



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



24RTC4840 2X4 Led Trof CNT BSKT 40K

Cooper Lighting Solutions

| | |
|------------------|--|
| Catalog Number | 24RTC4840 |
| Manufacturer | Cooper Lighting Solutions |
| Description | 2X4 Led Troffer, 4800 Lumens, 4000K, 80 Cri (Min), 0-10V Dimming to 5 PCT |
| Weight per unit | 17.6 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|---------------|
| amperage rating | 0.14A at 277V |
| Ballast Type | N/A |
| Lamp Type | LED |
| Material | Steel |
| Number of Lamps | 1 |
| Voltage Rating | 120-277V |

Material, Color, and Finish

| | |
|-------|---------|
| Style | (blank) |
|-------|---------|

Descriptions

| | |
|------------------------|--|
| Description | 2X4 LED TROF CNT BSKT 40K |
| extra long description | CLS 24RTC4840 2X4 LED TROFFER 4800 |
| Long Description | 2x4 LED Troffer, 4800 lumens, 4000K, 80 CRI (min), 0-10V Dimming to 5 pct |
| Product Type | 2X4 Led Troffer 4800 Lumen 40K 0 to 10V |
| Special Features | Shallow plenum - under 2.5" deep RTC fits the most challenging spaces |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | METALUX |
| GTIN | 00080083802630 |
| Manufacturers Part Number | 24RTC4840 |
| UPC | 080083802630 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED ARCHITECTURAL & SPECIFICATION LIGHTING |
| Type | RECESSED |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 17.55 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|--|
| Application | lighting |
| Mounting | Recessed |
| standard | cULus Listed - Damp Location;25 Degree C Ambient Temperature Rating;IC Rated;RoHS Compliant |