



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



24SRDL248CUNVL84 2X4 Led Layin 40K 4800LM

Cooper Lighting Solutions

Catalog Number	24SRDL248CUNVL84
Manufacturer	Cooper Lighting Solutions
Description	Led Troffer, 120 to 277 V Ac, 0.138 A @ 277 V, 38.2 W, Acrylic (Lens);Aluminum (Frame) Material, Matte White Enamel (Frame), 4000 K, 80, 100000 H Average Life, Dimmable, 4800 LM Brightness (Lumens), 47-15/16 In Length, 23-3/4 In Width, 4-11/16 In Height, 24 LB
Weight per unit	28.0 (lbs/each)
Product Category	Led Recessed Architectural & S

Features

amperage rating	0.138 at 277V
Ballast Type	N/A
Lamp Type	LED
Number of Lamps	1
Socket Type	N/A

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	2X4 LED LAYIN 40K 4800LM
extra long description	CLS 24SR-LD2-48-C-UNV-L840-CD1-U SR

Manufacturer Information

Brand	METALUX
GTIN	00080083752485
UPC	080083752485

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Recessed Static

Packaging

Carton	1
Weight Per each	28

Uses, Certifications, and Standards

Mounting standard	Recessed UL Recognized;cULus Listed;LM79/LM80 Compliant;DLC Qualified;IC Rated;RoHS Compliant;Damp Locations Listed;NOM Certified;25 Degree C Ambient Temperature Rating
-------------------	---