

Connectors - Zinc

Images





Download Photo Image Dimension A in Inches: 1 Dimension B in Inches: 2-1/4 Dimension C in Inches: 5

Download Dimensional Image

Bridgeport Fittings Inc. 705 Lordship Blvd. Stratford, CT 06615

Phone: 203-377-5944 Fax: 203-381-3488

Application

Used to join steel EMT to box or enclosure. Concretetight. 2 1/2" thru 4" suitable for use with Steel EMT. Insulator rated 105°C. 2-1/2" through 4" also listed for use with Steel and Aluminum Rigid Conduit. CSA Listed Raintight/For Use in Wet Locations in Canada Only

Product Information

Material: Zinc Die Cast Ball burnished, mirror smooth Finish:

Certifications & Codes:

CSA File Number: LR39354 Federal Specification Number: A-A-50553 **NEMA Standard:** FB-1 UL File Number: E24001 UL Standard: UL-514B **UNSPSC:** 39121434

Catalog ID: 258-DCl2

UPC Number: 781747162588

Description: Connector, Compression, Zinc Die Cast, 105°C Insulated Throat, Size 3 1/2 Inch

Application: Used to join steel EMT to box or enclosure. Concrete-tight. 2 1/2" thru 4" suitable for use with Steel EMT. Insulator rated 105°C. 2-1/2" through 4" also listed for use with Steel and Aluminum Rigid Conduit. CSA Listed Raintight/For Use in Wet Locations in Canada Only

Trade Size: 3-1/2"

Country of Manufacture: USA

Std Pkg Qty: 6

Unit Qty: Bulk