




GE
Lighting

69167 - 38PAR30H/SP10
38PAR30H/SP10



GENERAL CHARACTERISTICS

| | |
|---------------------|--------------------------|
| Lamp Type | Halogen - PAR |
| Bulb | PAR30 |
| Base | Medium Skirt (E26/50x39) |
| Filament | CC-8 |
| Rated Life (NOM) | 1500.0 h |
| Bulb Material | Sodalime glass |
| Primary Application | Indoor Floodlight |

PHOTOMETRIC CHARACTERISTICS

| | |
|---------------------------------------|----------|
| Initial Lumens (NOM) | 580.0 |
| Center Beam Candlepower (CBCP) (NOM) | 5700.0 |
| Color Rendering Index (CRI) (NOM) | 100.0 |
| Beam Spread (NOM) | 10.0 ° |
| Nominal Initial Lumens per Watt (NOM) | 15.26316 |

ELECTRICAL CHARACTERISTICS

| | |
|---------------|-----------|
| Wattage (NOM) | 38.0 |
| Voltage (NOM) | 120.0 |
| Burn Position | Universal |

DIMENSIONS

| | |
|------------------------------------|-------------------|
| Maximum Overall Length (MOL) (NOM) | 3.620 in(91.9 mm) |
| Bulb Diameter (DIA) (NOM) | 3.750 in(95.2 mm) |

PRODUCT INFORMATION

| | |
|----------------------------------|----------------|
| Product Code | 69167 |
| Description | 38PAR30H/SP10 |
| Standard Package | 00-Case |
| Standard Package GTIN | 10043168691670 |
| Standard Package Quantity | 6 |
| Sales Unit | Unit |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 6 |
| UPC | 043168691673 |