LED 2700K Low Profile LED Downlight - WH

43845WHLED27 (White)

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____



Dimensions

Height	1.25"
Width	6.00"

Ordering Information

Product ID	43845WHLED27
Finish	White
Available Finishes	WH, WH

Dimensions

Height from center of Wall opening	3.00"

Photometrics

Kelvin Temperature	2700K
Color Rendering Index	90

Specifications

Material	Aluminum
Diffuser Description	Textured Plastic

Electrical

Voltage	120V

Qualifications

Safety Rated	Wet Indoor Ceiling / Damp covered ceiling outdoor
Energy Star	Yes
ADA Compliant	Yes
Expected Life Span	40,000 hrs
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	LED
Lamp Included	Integrated
Delivered Lumens	535
Delivered Efficacy	44

Kichler
7711 East Pleasant Valley Road
Cleveland, Ohio 44131-8010
Toll free: 866.558.5706 or kichler.com

Notes:
1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.

KICHLER