#### RACO BELĽ C HUBBELL

D04

# SINGLE GANG BOXES - 2 IN. TO 2-5/8 IN. DEEP

# 2-5/8 in. Deep, with Lugs - Three Threaded Outlets - 4-1/2 in. x 2-3/4 in.

N/A



Catalog #: 5386-0

#### APPLICATIONS

For use in branch circuit wiring in wet, damp, or dry locations May be used as a weatherproof junction box, or as a housing for receptacles, switches, and GFCI's

### PRODUCT FEATURES

Reinforced connector outlets

State-of-the-art powder coat finish provides maximum weatherability and scratch resistance Eight box mounting options with detachable lugs Two closure plugs included

Hubs accept all threaded fittings and threaded conduit Ground screw installed

Multi-lingual instructions in each package Includes gasket and mounting hardware

N/A

## UL LISTED

File E195978

#### CSA

C22.2 No. 18

### NEMA

3R Rated

GENERAL PRODUCT INFORMATION Color:	Gray
CONFIGURATION Number Of Outlets: Gangs:	3 1
PRODUCT MEASUREMENTS Depth: Outlet Size: Cubic Inches (cm3): Wt. Ea. (Lbs.):	2-5/8 in. 3/4 in. 22.5 (368.7) 0.000
PACKAGING Package Type:	Shrink

Package Type: Std. Pkg.: Product UPC-A Labeled: Ship Carton Length (in.): Ship Carton Width (in.): Ship Carton Height (in.): Ctn Weight (Lbs.): Pallet Qty: UPC Number: I2of5:

ink 15 Yes 16.19 6.50 8.50 12.40 1350.00 050169538609 50050169538604