



Slide fan support - same heavy-duty slide as 55501, but with 2.0-inch deep box, to accommodate up to 1-inch firewall or soundproofed ceilings, with rotating dual support for 16-24-inch spans, bulk packed. 25-Pack.

Features & Benefits

For spans from 16 to 24 inches.

Peel-off tape for "hands-free" installation.

Broadest line available, from shallow to deep boxes.

Boxes include top knockouts.

UL listed for fan and fixture support.

Maximum weight rating shown for 16 inch spans.

Pre-assembled with ground screw installed.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007266894	Country Of Origin	China
Material	Cold Rolled Steel	Features	Fan Rated, Fixture Rated
Number of Knockouts	2	Application Sector	Commercial, Residential
Standard	Residential/Commercial	Warranty Type	1-Year Limited Warranty
Type	Ceiling Box		

Dimensions

Product Depth US	2.0 in	Cubic Capacity	21 in ³
------------------	--------	----------------	--------------------

Technical Information

Number of Gangs	1	Fan Rating	70 lb
Indoor/Outdoor	Indoor	Cable Entry	Back
Box Shape	Round	Mounting Type	Stud Mount