
GE Lighting

# 46855 - 65R30/FL


GE BR30

Energy Savings










**CAUTIONS & WARNINGS**

**Warning**

• Unexpected lamp rupture may cause injury, fire, or property damage
  - Avoid direct water, liquid or metal contact.
• Risk of Fire
  - Keep combustible materials away from lamp.

## GENERAL CHARACTERISTICS

| | |
|---|---|
| Lamp Type | Incandescent - Reflector |
| Bulb | BR30 |
| Base | Medium Screw (E26) |
| Filament | CC-6 |
| Rated Life | 2000.0 hrs |
| Life in Years | 1.8 |

## PHOTOMETRIC CHARACTERISTICS

| | |
|---|---|
| Initial Lumens | 670.0 |
| Color Temperature | 2600.0 K |
| Nominal Initial Lumens per Watt | 11 |

## ELECTRICAL CHARACTERISTICS

| | |
|---|---|
| Wattage | 65.0 |
| Voltage | 130.0 |
| Estimated Energy Cost per Year | 7.83 |

## DIMENSIONS

| | |
|---|---|
| Maximum Overall Length (MOL) | 5.3700 in(136.4 mm) |
| Bulb Diameter (DIA) | 3.750 in(95.2 mm) |

## PRODUCT INFORMATION


| | |
|---|---|
| Product Code | 46855 |
| Description | 65R30/FL |
| Standard Package | BUNDLE |
| Standard Package GTIN | 00043168468558 |
| Standard Package Quantity | 30 |
| Sales Unit | Unit |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 30 |
| UPC | 043168142632 |

GE Lighting

# 46855 - 65R30/FL


GE BR30

Energy Savings










**CAUTIONS & WARNINGS**

**Warning**

• Unexpected lamp rupture may cause injury, fire, or property damage
  - Avoid direct water, liquid or metal contact.
• Risk of Fire
  - Keep combustible materials away from lamp.

## GENERAL CHARACTERISTICS

| | |
|---|---|
| Lamp Type | Incandescent - Reflector |
| Bulb | BR30 |
| Base | Medium Screw (E26) |
| Filament | CC-6 |
| Rated Life | 2000.0 hrs |
| Life in Years | 1.8 |

## PHOTOMETRIC CHARACTERISTICS

| | |
|---|---|
| Initial Lumens | 670.0 |
| Color Temperature | 2600.0 K |
| Nominal Initial Lumens per Watt | 11 |

## ELECTRICAL CHARACTERISTICS

| | |
|---|---|
| Wattage | 65.0 |
| Voltage | 130.0 |
| Estimated Energy Cost per Year | 7.83 |

## DIMENSIONS

| | |
|---|---|
| Maximum Overall Length (MOL) | 5.3700 in(136.4 mm) |
| Bulb Diameter (DIA) | 3.750 in(95.2 mm) |

## PRODUCT INFORMATION

| | |
|---|---|
| Product Code | 46855 |
| Description | 65R30/FL |
| Standard Package | BUNDLE |
| Standard Package GTIN | 00043168468558 |
| Standard Package Quantity | 30 |
| Sales Unit | Unit |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 30 |
| UPC | 043168142632 |