



Pass and Seymour
Discontinued - Non-Grounding Combination Switches - Sub 690G
Part No. 690

Single-Pole, Double Switch, 15A, 120/277V



Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	690G
Color	Brown	UPC Number	785007690019
Country Of Origin	Mexico	Application Sector	Commercial, Residential
Standard	UL20		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Configuration	N-O	Operating Cycles	30000
Actuator	Toggle	Connection	Side wire, non-grounding
Contact Rating	15Amp, 120/277Vac	Amperage	15 A
Action	(2) SP	Number of Poles	Single Pole
Location Rating	Dry	Voltage	0.433 V
Environmental Conditions	Flammability: UL94 V2		