

Specifications



Photo is representative



Eaton 7623W-BOX

Eaton commercial grade decorator switch, Box, #14-10 AWG, 20A, Flush, 120/277V, Back/push, Antimicrobial paddle, Maintained, White, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Three-way, Thermoplastic 647390

General specifications

PRODUCT NAME	Eaton commercial grade decorator switch
CATALOG NUMBER	7623W-BOX
UPC	032664647390
PRODUCT LENGTH/DEPTH	1.29 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	1.18 in
PRODUCT WEIGHT	0.24 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Listed cULus Listed
PRODUCT TYPE	Commercial grade decorator switch



Powering Business Worldwide

Product specifications

ALLOWABLE WIRE SIZE	#14-10 AWG
SPECIAL FEATURES	Box
TYPE	Switch decorator
AMPERAGE RATING	20A
VOLTAGE RATING	120/277 V
NUMBER OF POLES	Three-way
PHASE	Single-phase
WIRING METHOD	Back and push
SWITCH TYPE	Three-way
MOUNTING METHOD	Flush
CLOSURE TYPE	Maintained
LOAD TYPE	CFL Fan LED INC Motor Control ELV FLR HAL MLV
MATERIAL	Thermoplastic
ACTUATOR	Antimicrobial paddle
COLOR	White

Resources

	Eaton Specification Sheet - 7623W-BOX
SPECIFICATIONS AND DATASHEETS	Arrow Hart commercial specification grade AC decorator switches spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

