Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



85068 TLC RG-6 F Tool-Less Compression Conn, 10/Card

Ideal

Catalog Number	85068
Manufacturer	Ideal
Description	Tool-Less Compression Connector, Type F Connection, RG 6 Coax Cable, Gray, 0.01 LB/Ea
Weight per unit	0.0600 (lbs/each)
Product Category	Coaxial & Twinaxial Connectors

Descriptions

Description	TLC RG-6 F TOOL-LESS COMPRESSION CONN, 10/CARD
extra long description	IDEAL 85-068 RG6 F TOOL-LESS CMPRCO
Features	Connector Model: 6FTLCTool-Less Compression connectorAccepts RG-6 coax cablesCenter conductor range: AllDielectric diameter range: .175” - .183”Outer jacket diameter range: .254” - .278”Recommended cable prep/stripping tools: 45-605 PrepPRORecommended compression tools: Not requiredConnector color: GrayThe new TLC (Tool-Less Compression) RG-6 F compression connector is our simplest, fastest, and lowest total cost solution for installing compression connectors. Designed to save the installer time, labor, an

Manufacturer Information

Brand	Ideal
GTIN	00783250850686
sub brand	TLC „
UPC	783250850686

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Tool-Less Compression Connector - RG6

Availability

minimum qty	10

Packaging

Carton	10
Weight Per each	0.06

Uses, Certifications, and Standards

standard	RoHS Compliant