ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



# 89045 Omniconn RG-6 Quad F CMPRSN Conn Black, 50/Jar

*Ideal*

| | |
|---|---|
| Catalog Number | 89045 |
| Manufacturer | Ideal |
| Description | Ideal, Compression Connector, Omniconn, F-Type, Material: Brass, Finish: Nickel-Plated, Nominal Impedance: 75 Ohm, Ports Size: 7/16 In, Coaxial Cable Type: RG-6, Bandwidth: 3 GHZ, Dielectric Diameter: 0.175 - 0.183 In, Overall Jacket Diameter: 0.260 - 0.280 In |
| Weight per unit | 0.9500 (lbs/each) |
| Product Category | Coaxial & Twinaxial Connectors |

## Features

| | |
|---|---|
| Material | Brass |

## Material, Color, and Finish

| | |
|---|---|
| Finish | Nickel |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Descriptions

| | |
|---|---|
| Description | OMNICONN RG-6 QUAD F CMPRSN CONN BLACK, 50/JAR |
| extra long description | IDEAL 89-045 RG6 QUAD COMPR CONN,OM |
| Features | Connector Model: 6QFOCAccepts RG-6 Quad coax cablesCenter conductor range: AllDielectric diameter range: .175” - .183”Outer jacket diameter range: .270” - .295”Recommended cable prep/stripping tools: 45-605 PrepPRO; 45-526Recommended compression tools: 30-793 OmniSeal PRO XL; 33-632 Linear X3The IDEAL OmniConn F connector is a cable specific connector solution for RG-6 coax. The OmniConn connectors have a combination brass and plastic exterior and an inner O-ring to provide a weather proof connection suita |
| Long Description | IDEAL, Compression Connector, OmniCONN, F-Type, Material: Brass, Finish: Nickel-Plated, Nominal Impedance: 75 OHM, Ports Size: 7/16 IN, Coaxial Cable Type: RG-6, Bandwidth: 3 GHZ, Dielectric Diameter: 0.175 - 0.183 IN, Overall Jacket Diameter: 0.260 - 0.280 IN |
| Product Type | RG6 Quad Compr Conn, Omni, 50JR |
| Special Features | Features: OmniCONN F compression connectors install easily onto standard RG 6 and RG 6Quad cables; Non corrosive nickel plated brass body and polycarbonate bushing; Delrin/Nylon adapter sleeve and o-ring provide double protection for a watertight seal; Free spinning hex nut for ease of installation onto all 7/16 IN ports 75 OHM nominal impedance; Bandwidth up to 3 GHZ; Nominal Impedance: 75 OHM; Ports Size: 7/16 IN; Coaxial Cable Type: RG-6; Bandwidth: 3 GHZ; Dielectric Diameter: 0.175 - 0.183 IN; Overall |

## Manufacturer Information

| | |
|---|---|
| Brand | Ideal |
| GTIN | 00783250890453 |
| Manufacturers Part Number | 89-045 |
| sub brand | OmniCONN |
| UPC | 783250890453 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | WIRE NUTS |
| Type | F-Type |

## Availability

| | |
|---|---|
| minimum qty | 50 |

## Packaging

| | |
|---|---|
| Carton | 50 |
| Weight Per each | 0.95 |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Terminating an F Style connection onto RG 6 Quad Coax . |