ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AN19GN0A5E045 C440 9-45A SZ 2 FVNR STR 120VAC STD

Eaton Corp

Catalog Number	AN19GN0A5E045
Manufacturer	Eaton Corp
Description	Eaton Freedom Nema Starter, Full Voltage Non-Reversing, C440 Electronic Overload Relay, Nema Size 2 Open Enclosure - 45 A, Horizontal Mounting, 120/60 or 110/50 Coil Voltage, C440 Standard Feature Set - 9–45 A
Weight per unit	3.9 (lbs/each)
Product Category	Nema Combination Starters

Features

Coil Voltage	120/60 or 110/50
dimensions	4.9800 IN X 2.6000 IN X 7.1000 IN

Dimensions and Weight

Size	2

Descriptions

Description	C440 9-45A SZ 2 FVNR STR 120VAC STD
extra long description	ETN AN19GN0A5E045 FDM STR FVNR SZ2
Features	Eaton's Freedom starters and contactors feature a compact, space-saving design, using state-of-the-art technology and the latest in high strength, impact and temperature resistant insulating materials. In addition to the bimetallic overload, Eaton also offers a series of electronic overload relay (C440) available as a standalone unit and assembled with Freedom contactor.
Long Description	Eaton Freedom NEMA Starter, Full voltage non-reversing, C440 electronic overload relay, NEMA Size 2 open enclosure - 45 A, Horizontal mounting, 120/60 or 110/50 coil voltage, C440 standard feature set - 9–45 A
Product Type	FDM STR FVNR SZ2 120V C440-ST 9-45a
Special Features	With C440 EOLR standard feature set, SEL reset, SEL class (10a, 10, 20, 30)

Manufacturer Information

Brand	Eaton
GTIN	00786685415420
Manufacturers Part Number	AN19GN0A5E045
UPC	786685415420

Taxonomies, Classifications, and Categories

Type	Motor control starter

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	3.9199

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels and EOEMs
Mounting	HORIZONTAL
NEMA Frame Size	NEMA Size 2
standard	NEMA,CSA,CE,UL,RoHS Compliant