

# NEER Zinc Bushed Conduit Nipples

## CNN: Zinc

### Applications

- Use through knockout to connect box to conduit coupling.
- Use with a locknut to connect two boxes side by side or back to back.
- Use with a locknut to connect fixture housings to continuous runs.

### Features

- Male hub threads — NPS.
- Available with insulated throat.

### Material/Finish

- Zinc die cast

### Certifications and Compliances

- UL Standard: 514B
- UL Listed: E14814
- CSA Standard: C22.2 No. 18
- CSA Certified: 065178
- NEMA: FB-1



CNI-100

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters	
		Maximum Diameter	Body Length
<b>Without Insulated Throat</b>			
1/2	<b>CNN-100</b>	0.94/23.9	0.59/15.0
3/4	<b>CNN-200</b>	1.19/30.2	0.72/18.3
1	<b>CNN-300</b>	1.38/35.1	0.85/21.6
1-1/4	<b>CNN-400</b>	1.74/44.2	0.87/22.1
1-1/2	<b>CNN-500</b>	2.12/53.8	0.90/22.9
2	<b>CNN-600</b>	2.55/64.8	1.15/29.2
2-1/2	<b>CNN-700</b>	3.21/81.5	1.43/36.3
3	<b>CNN-800</b>	3.80/96.5	1.43/36.3
3-1/2	<b>CNN-900</b>	4.27/108.5	1.43/36.3
4	<b>CNN-1000</b>	4.79/121.7	1.43/36.3

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters	
		Maximum Diameter	Body Length
<b>With Insulated Throat</b>			
1/2	<b>CNI-100</b>	0.94/23.9	0.67/17.0
3/4	<b>CNI-200</b>	1.19/30.2	0.80/20.3
1	<b>CNI-300</b>	1.38/35.1	0.93/23.6
1-1/4	<b>CNI-400</b>	1.74/44.2	0.95/24.1
1-1/2	<b>CNI-500</b>	2.12/53.8	0.98/24.9
2	<b>CNI-600</b>	2.55/64.8	1.23/31.2

COMMERCIAL PRODUCTS: RIGID AND IMC FITTINGS

Commercial Products