




**Atlanta, Georgia**

**Phone 800-521-7326**

**Fax 770-745-1333**

**Channel Nut Regular Spring  
Zinc Plated & 316 Stainless Steel  
For Use With 1-3/8 and 1-5/8 Deep Strut**



| Peco Catalog# | Thread Pitch (TH) | Thickness Of Nut (Inches) | Thickness Of Nut (Millimeters) |
|---------------|-------------------|---------------------------|--------------------------------|
| CNR20025EG    | 1/4"-20           | 0.25                      | 6.3                            |
| CNR20031EG    | 5/16"-18          | 0.25                      | 6.3                            |
| CNR30031EG    | 5/16"-18          | 0.37                      | 9.4                            |
| CNR20037EG    | 3/8"-16           | 0.25                      | 6.3                            |
| CNR30037EG    | 3/8"-16           | 0.37                      | 9.4                            |
| CNR30050EG    | 1/2"-13           | 0.37                      | 9.4                            |
| CNR40050EG    | 1/2"-13           | 0.50                      | 12.7                           |
| CNR40062EG    | 5/8"-11           | 0.50                      | 12.7                           |
| CNR40075EG    | 3/4"-10           | 0.50                      | 12.7                           |
| CNR40087EG    | 7/8"-9            | 0.50                      | 12.7                           |




**Atlanta, Georgia**

**Phone 800-521-7326**

**Fax 770-745-1333**

**Channel Nut Regular Spring  
Zinc Plated & 316 Stainless Steel  
For Use With 1-3/8 and 1-5/8 Deep Strut**



| <b>Peco Catalog#</b> | <b>Thread Pitch (TH)</b> | <b>Thickness Of Nut (Inches)</b> | <b>Thickness Of Nut (Millimeters)</b> |
|----------------------|--------------------------|----------------------------------|---------------------------------------|
| CNR20025EG           | 1/4"-20                  | 0.25                             | 6.3                                   |
| CNR20031EG           | 5/16"-18                 | 0.25                             | 6.3                                   |
| CNR30031EG           | 5/16"-18                 | 0.37                             | 9.4                                   |
| CNR20037EG           | 3/8"-16                  | 0.25                             | 6.3                                   |
| CNR30037EG           | 3/8"-16                  | 0.37                             | 9.4                                   |
| CNR30050EG           | 1/2"-13                  | 0.37                             | 9.4                                   |
| CNR40050EG           | 1/2"-13                  | 0.50                             | 12.7                                  |
| CNR40062EG           | 5/8"-11                  | 0.50                             | 12.7                                  |
| CNR40075EG           | 3/4"-10                  | 0.50                             | 12.7                                  |
| CNR40087EG           | 7/8"-9                   | 0.50                             | 12.7                                  |