Product specifications

# Eaton CSAS3F3CY2205



## Catalog Number: CSAS3F3CY2205

Eaton Global Plus connector cable, Global Plus, Accessory, Sensor connectivity, Micro-style straight female, AC, 3-wre, 22 AWG, 16.4 ft, 3 pin, PVC, 320V

### General specifications

**Product Name**
Eaton Global Plus connector cable

**Catalog Number**
CSAS3F3CY2205

**UPC**
782116056903

**Product Length/Depth**
196.8 in

**Product Height**
0.58 in

**Product Width**
0.58 in

**Product Weight**
0.9 lb

**Warranty**
1 year

**Certifications**
UL Listed
CSA Certified

Powering Business Worldwide

## defaultTaxonomyAttributeLabel

### Type

Accessory

### Cord length

196.8 ft

### Operating Temperature

-13° to 176°F (-25° to 80°C)

### Cable type

Polyvinyl Chloride (PVC)

### Connection

Micro-style straight female

### Number of wires

3

### Wire size

#22 AWG

### Environmental rating

IP67

### Input voltage

320 V

### Series

Global Plus

### Switch type

Sensor connectivity

### Power consumption

AC

### Number of pins

3

## Resources

### Catalogs

Volume 6: Solid-State Motor Control

Eaton's Volume 8—Sensing Solutions

### Specifications and datasheets

Eaton Specification Sheet - CSAS3F3CY2205




Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Product specifications

# Eaton CSAS3F3CY2205



## Catalog Number: CSAS3F3CY2205

Eaton Global Plus connector cable, Global Plus, Accessory, Sensor connectivity, Micro-style straight female, AC, 3-wre, 22 AWG, 16.4 ft, 3 pin, PVC, 320V

### General specifications

**Product Name**
Eaton Global Plus connector cable

**Catalog Number**
CSAS3F3CY2205

**UPC**
782116056903

**Product Length/Depth**
196.8 in

**Product Height**
0.58 in

**Product Width**
0.58 in

**Product Weight**
0.9 lb

**Warranty**
1 year

**Certifications**
UL Listed
CSA Certified

Powering Business Worldwide

## defaultTaxonomyAttributeLabel

### Type

Accessory

### Cord length

196.8 ft

### Operating Temperature

-13° to 176°F (-25° to 80°C)

### Cable type

Polyvinyl Chloride (PVC)

### Connection

Micro-style straight female

### Number of wires

3

### Wire size

#22 AWG

### Environmental rating

IP67

### Input voltage

320 V

### Series

Global Plus

### Switch type

Sensor connectivity

### Power consumption

AC

### Number of pins

3

## Resources

### Catalogs

Volume 6: Solid-State Motor Control

Eaton's Volume 8—Sensing Solutions

### Specifications and datasheets

Eaton Specification Sheet - CSAS3F3CY2205




Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia