Switches, Single Pole 20A, 120-277V AC Specification Grade Commercial Switch

Features

- Thread cleaning captive mounting screw
- Abuse resistant nylon toggle
- Steel, zinc plated bridge is corrosion resistant

Ordering Information

Description Toggle, back and side wired	Toggle Color Ivory	UPC 783585154046	Catalog Number CSB120I
-----------------------------------------------	-----------------------	---------------------	---------------------------


Listings

UL Listed CSA Certified Fed. Spec. W-S-896

Specifications

•	
Top Material	Thermoplastic, Gray
Base Material	Thermoplastic, Black
Toggle Material	Nylon
Contacts	Silver Alloy
Terminal Screws	Brass
Auto Grounding Mounting Bridge	Zinc Plated Steel
Ground Screw	Brass (Green)

HUBBELL



Performance

Electrical

Dielectric Voltage	Withstands 1500V AC minimum for 1 minute
Max. Continuous Current	20A
Max. Working Voltage	277V AC
Overload	Minimum 4.8 times rated current for 100 cycles
Temperature Rise	30°C maximum at rated current

Mechanical

Terminal Accommodations #14 AWG min. - #10 AWG max. solid and stranded copper wire only

Environmental

Flammability Operating Temperature UL 94V-2 Max. continuous: 75°C; Min. continuous: -40°C without impact

Online Resources

Customer Use Drawing	
eCatalog	



Dimensions in Inches (mm) Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.