Product specifications

Eaton DC1-12011NB-A20CE1



Photo is representative

Catalog Number: DC1-12011NB-A20CE1

Eaton DC-1 drive, IP20 240V 1PH IN/3PH OUT 3HP, 10.5A ENH FW

General specifications

Product Name
Eaton PowerXL DC1 adjustable frequency drive

Catalog Number
DC1-12011NB-A20CE1

UPC
786687019282

Product Length/Depth
10.25 in

Product Height
9 in

Product Width
5.5 in

Product Weight
4.1 lb

Warranty
Eaton Selling Policy 25-000, one (1) year from the date of installation of the product or eighteen (18) months from the date of shipment of the product, whichever occurs first. Plus 5 years on capacitor cells.

Certifications
cUL Certified
EN 61800-3
UkrSepro
EN 60529
UL Listed
EN 61800-5-1

Powering Business Worldwide

defaultTaxonomyAttributeLabel

Line voltage

240V

Protection filtering

IP20

Type

VF drive

Number of inputs

1

Frame

2

Number of outputs

3

Rated operational current

10.5 A

Resources

Catalogs

Product Datasheet - DC1-12011NB-A20CE1

Specifications and datasheets

Eaton Specification Sheet - DC1-12011NB-A20CE1

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia