Product specifications

Eaton DC1-32030NB-A20CE1

Catalog Number: DC1-32030NB-A20CE1

Eaton PowerXL DC1 series Adjustable Frequency Drives, IP20 240V 3PH IN/3PH OUT 10HP, 30A ENH FW



Photo is representative

General specifications

Product Name
Eaton PowerXL DC1 adjustable frequency drive

Catalog Number
DC1-32030NB-A20CE1

UPC
786687020011

Product Length/Depth
22.1 in

Product Height
13.3 in

Product Width
11.4 in

Product Weight
22.2 lb

Warranty
Eaton Selling Policy 25-000, one (1) year from the date of installation of the product or eighteen (18) months from the date of shipment of the product, whichever occurs first. Plus 5 years on capacitor cells.

Certifications
cUL Certified
EN 61800-3
UkrSepro
EN 60529
UL Listed
EN 61800-5-1

Powering Business Worldwide

defaultTaxonomyAttributeLabel

Type

VF drive

Frame

4

Rated operational current

30 A

Resources

Catalogs

Product Datasheet - DC1-32030NB-A20CE1

Specifications and datasheets

Eaton Specification Sheet - DC1-32030NB-A20CE1

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services

---

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia